
Ultra-Low-Noise Current Amplifier



| Features | Bandwidth and Frequency Response Independent of Detector-Capacitance (up to 10 nF) Extremely Low Noise, 14 fA/√Hz Equivalent Input Noise Current Bandwidth DC 20 kHz Transimpedance (Gain) 2 x 10⁸ V/A Photodiode- and Photomultiplier-Amplifier Spectroscopy Charge-Amplifier Ionisation Detectors Preamplifier for Lock-Ins, A/D-Converters, etc. | |
|--------------------------|--|---|
| Applications | | |
| Specifications | Test Conditions | $Vs = \pm 15 \text{ V}, Ta = 25^{\circ}C$ |
| Gain | Transimpedance Accuracy | 2×10^8 V/A (>10 k Ω Load) $\pm 1\%$ |
| Frequency Response | Lower Cut-Off Frequency Upper Cut-Off Frequency Rise- / Fall-Time Gain Flatness | DC 20 kHz (- 3 dB) 20 μs (10% - 90%) ± 0.1 dB |
| Input | Equ. Input Noise Current Equ. Input Noise Voltage Input Bias Current Input Bias Current Drift Offset Current Compensation Max. Input Current Input Offset Voltage DC Input Impedance | 14 fA/ $\sqrt{\text{Hz}}$ (@ 10 kHz) 5 nV/ $\sqrt{\text{Hz}}$ (@ 10 kHz) 2 pA typ. Factor 1.7 / 10 K \pm 15 nA, Adjustable by Offset-Trimpot \pm 50 nA (Linear Amplification) < 1 mV 50 Ω (Virtual) // 5 pF |
| Output | Output Voltage Output Impedance Max. Output Current | \pm 10 V (>10 k Ω Load) 50 Ω (Terminate with >10 k Ω for best Performance) \pm 10 mA (Linear Amplification) |
| Power Supply | Supply Voltage Supply Current | \pm 15 V \pm 40 mA typ. |
| Case | Weight Material | 210 gr. (0.5 lbs) AlMg4.5Mn, nickel-plated |
| Temperature Range | Storage Temperature Operating Temperature | -40 +100 °C 0 +60 °C |
| Absolute Maximum Ratings | Input Voltage Power Supply Voltage | ± 5 V ± 22 V |


Ultra-Low-Noise Current Amplifier

Connectors Input BNC

Output BNC

Power Supply LEMO Series 1S, 3-pin Fixed Socket

Pin 1: + 15V Pin 2: - 15V Pin 3: GND



Application Diagrams

Photo Detector Biasing in Photovoltaic Mode: Use for Low Speed Applications and Minimum Dark Current.






Photo Detector Biasing in Photoconductive Mode: Use for Fast Applications and if More Dark Current is Tolerable. Bias Voltage Decreases Detector Capacitance.



Datasheet LCA-20K-200M

Ultra-Low-Noise Current Amplifier

Dimensions



FEMTO Messtechnik GmbH Paul-Lincke-Ufer 34 D-10999 Berlin • Germany Tel.: +49 (0)30 - 4 46 93 86 Fax: +49 (0)30 - 4 46 93 88 e-mail: info@femto.de

http://www.femto.de

Specifications are subject to change without notice. Information furnished herin is believed to be accurate and reliable. However, no responsibility is assumed by FEMTO Messtechnik GmbH for its use, nor for any infringement of patents or ather rights granted by implication or otherwise under any patent rights of FEMTO Messtechnik GmbH. Product names mentioned may also be trademarks used here for identification purposes only.

© by FEMTO Messtechnik GmbH
Printed in Germany

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

F E T O