

PhlatLight[®] LED Development Kit Product Brief

DK-105T-1



Overview

PhlatLight DK-105T-1 development kit is a comprehensive solution designed specifically to support development of PhlatLight SST-90 and SST-50 based solutions. The kit includes highly versatile drivers and control circuitry, efficient thermal management solutions, clean interfaces, and cabling for use with standard laboratory equipment. The inclusion of these components ensures the PhlatLight SST-90 and SST-50 LED modules can be operated optimally at any drive condition. Whether this is low power for maximum efficiency, high power for maximum brightness or anywhere in between, the PhlatLight DK-105T Development Kit ensures the right performance.

This plug and play solution can easily be connected to standard laboratory equipment through standard connectors and allows system designers to save weeks in their development cycles.

Key Features

- Compatible with SST-90 and SST-50 PhlatLight LEDs
- Driver board supply currents of 1.75A, 3.2A and 5A
- On board PWM controller supports duty cycles ranging from 0% to 100%
- Dimmable using 0-10V analog input
- Included PAR-20 format Synjet cooling system
- Typical thermal resistance of 1.67°C/W to 2.5°C/W from heat sink to ambient
- Driver circuitry based off of TI TPS71530 IC

PhlatLight Evaluation Kit Contents

- 1 comprehensive driver board capable of providing 1.75A, 3.15A or 5A to the LED
- 1 high performance, Synjet thermal solution
- Simple interfaces to user supplied equipment
- Thermal interface materials and mounting hardware
- User manual including step-by-step instructions for set-up and operation of the kit.

User Equipment Required

- Standard 12V/50W power supply.
- Standard laboratory instrumentation - volt meter, oscilloscope, photodetector.
- 0-10V dimmer or power supply for dimming

Note: PhlatLight LED products are not included in the development kits and must be purchased separately.

Product Compatibility

Development Kit Part Number	Compatible PhlatLight LEDs
DK-105T-1	SST-90*, SST-50*

*Note *: Development kit thermal solution is predrilled for SSR-50 and SSR-90. It is recommended to specify SSR-90 or SSR-50 (SST-90 or SST-50 premounted on star format MCPCB) for evaluation.*

Ordering Information

Ordering Part Number	Product	Description
DK-105T-1	DK-105T PhlatLight Development Kit	Single channel development kit, with 5A driver, PAR-20 Synjet and user manual

The products, their specifications and other information appearing in this document are subject to change by Luminus Devices without notice. Luminus Devices assumes no liability for errors that may appear in this document, and no liability otherwise arising from the application or use of the product or information contained herein. None of the information provided herein should be considered to be a representation of the fitness or suitability of the product for any particular application or as any other form of warranty. Luminus Devices' product warranties are limited to only such warranties as accompany a purchase contract or purchase order for such products. Nothing herein is to be construed as constituting an additional warranty. No information contained in this publication may be considered as a waiver by Luminus Devices of any intellectual property rights that Luminus Devices may have in such information. PhlatLight® is a registered trademark of Luminus Devices, Inc., all rights reserved.

Luminus Devices
1100 Technology Park Drive
BillERICA, MA 01821

978-528-8000 (T)
978-528-8001 (F)

E-mail: sales@luminus.com

www.luminus.com