

CX3SM AT CRYSTAL

Low Profile Miniature SMD Crystal

9.6MHz to 250MHz

FEATURES

- Designed for surface mount applications, including infrared, vapour phase or epoxy mount techniques
- Hermetically sealed ceramic package
- **Excellent ageing characteristics**
- Available with glass or ceramic lid
- High shock and vibration resistance
- Custom designs available
- Full Military testing available

SPECIFICATION

Specifications stated are typical at 25°C unless otherwise indicated. Specifications may change without notice.

Fundamental Frequency:	10.0MHz	32.0MHz	155.52MHz
Motional Resistance R (Ω):	60	25	10
Motional Capacitance C1 (fF):	2.8	6.2	4.0
Quality Factor Q (k):	95	30	30
Shunt Capacitance C0 (pF):	1.4	2.3	2.3

Calibration Tolerance1: ±100ppm or tighter as required

Load Capacitance2: 20pF for fr. <50MHz

10pF for fr. >50MHz

 $500\mu W$ max. for fr. <50MHz Drive Level: $200\mu W$ max. for fr. <50MHz

Temperature Stability³

Commercial -10 ~ +60°C: ± 50 ppm to ± 10 ppm Industrial -40 to +85°C: ±100ppm to ±20ppm Military -55 to +125°C: ±100ppm to ±30ppm

Ageing, first year4: 5ppm max.

Better than ±1ppm is available

Shock, survival⁵: 3,000g, 0.3ms, 1/2 sine Vibration, survival6: 20g, 10~2000Hz swept sine

Operating Temperature Range

Commercial: -10° to +70°C -40° to +85°C Industrial: Military: -55 to +125°C Storage Temperature Range: -55° to +125°C

Maximum Process Temperature: +260°C for 20 seconds


- 1. Other tolerances available, contact Euroquartz sales.
- 2. Unless specified otherwise.
- 3. Does not include calibration tolerance. The characteristicsof the frequency stability over temperature follow that of the AT thicknessshear mode.
- 4. 5ppm max. for frequencies below 40MHz For tighter tolerances and higher frequencies contact Euroquartz sales.
- 5. Higher shock version available. See CX1HGSM
- 6. Per MIL-STD-202G, Method 204D, Condition D. Random vibration testing also available.

DESCRIPTION



CX3SM AT crystals in leadless ceramic packages are designed for surface mounting on PCB or hybrid substrates. The small footprint, low profile crystal is ideal for a wide range of commercial, industrial, medical and defence/aerospace applications.

OUTLINE & DIMENSIONS




Dim. H	Glass Lid	Ceramic Lid
SM1	1.35	1.70
SM2	1.40	1.75
SM3	1.47	1.83
SM4	1.40	1.75
SM5	1.47	1.83

PACKAGING OPTIONS

CX3SM AT crystals are available either tray packed (<250pcs) or tape and reel (>250 pieces).

16mm tape, 178mm or 330mm reels (EIA 418).

CRYSTAL EQUIVALENT CIRCUIT



R1 Motional Resistance C1 Motional Capacitance

L1 Motional Inductance C0 Shunt Capacitance

HOW TO ORDER CX3SM AT CRYSTALS

